

# Eaton DILM17-10(24V60HZ)

Catalog Number: DILM17-10(24V60HZ)

Eaton XT IEC mini contactor, 17A, 24 Vac, 60 Hz, 1NO, 18A, Frame C, 45 mm, 60 Hz, 2, 3/5, 5, 10, 15 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Screw terminals, FVNR, 7.5 kW

## General specifications



Photo is representative

### Product Name

Eaton XT IEC mini contactor

### Catalog Number

DILM17-10(24V60HZ)

### EAN

4015082769956

### Product Length/Depth

1.8 in

### Product Height

3.3 in

### Product Width

3.8 in

### Product Weight

0.92 lb

### Warranty

1 year

### Compliances

CE Marked

RoHS Compliant

### Certifications

CSA Certified

UL Listed

IEC 60947

EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Amperage Rating

17A

### HP rating - max

2, 3/ 5, 5, 10, 15 (1/3PH @120,240/208,240, 480, 600 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing miniature contactor

### Frequency rating

60 Hz

### Frame size

45 mm

### Terminals

Screw terminals

### Coil

24 Vac 60 Hz

### Coil voltage

24 Vac, 60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

18 A

### Series

XT IEC

### Operation

Non-reversing

### Power consumption

7.5 kW

## Resources

### Multimedia

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Contactors Explained

### Specifications and datasheets

Global Data Sheet - DILM17-10(24V60HZ)

Eaton Specification Sheet - DILM17-10(24V60HZ)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)