

# Eaton DILM17-10(RDC130)

Catalog Number: DILM17-10(RDC130)

Eaton XT IEC mini contactor, 17A, 110-130 Vdc, 1NO, 18A, Frame C, 45 mm, 50-60 Hz, 2, 3/ 5, 5, 10, 15 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, FVNR, 440V, 7.5 kW

## General specifications



Photo is representative

### Product Name

Eaton XT IEC mini contactor

### EAN

4015082770204

### Product Height

85 mm

### Product Weight

0.01 lb

### Certifications

IEC 60947

UL Listed

EN 60947

CSA Certified

### Catalog Number

DILM17-10(RDC130)

### Product Length/Depth

138 mm

### Product Width

45.03 mm

### Compliances

CE Marked

RoHS Compliant

**Amperage Rating**

17A

**HP rating - max**

2, 3/ 5, 5, 10, 15 (1/3PH @120,240/208,240, 480, 600 V)

**Number Of Poles**

Three-pole

**Type**

Full voltage non-reversing miniature contactor

**Frequency rating**

50-60 Hz

**Frame size**

45 mm

**Coil voltage**

110-130 Vdc

**Contact configuration**

1 NO

**Continuous ampere rating**

18 A

**Series**

XT IEC

**Operation**

Non-reversing

**Power consumption**

7.5 kW

**Multimedia**[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)[Contactors Explained](#)**Specifications and datasheets**[Eaton Specification Sheet - DILM17-10\(RDC130\)](#)[Product Data Sheet - DILM17-10\(RDC130\)](#)