

# Eaton DILM25-10(115V60HZ)

Catalog Number: DILM25-10(115V60HZ)

Eaton XT IEC large contactor, 25A, 115 Vac, 60 Hz, 1NO, 25A, Frame C, 45 mm, 60 Hz, 2, 5/7.5, 10, 15, 20 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, , Screw terminals, FVNR, 11 kW



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC large contactor	DILM25-10(115V60HZ)
<b>EAN</b>	<b>Product Length/Depth</b>
4015082771256	1.8 in
<b>Product Height</b>	<b>Product Width</b>
1.9 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.92 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
RoHS Compliant	EN 60947
	IEC 60947
	CSA Certified

## Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

25A

### HP rating - max

2, 5/7.5, 10, 15, 20 (1/3PH @120,240/208,240,480,600 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

60 Hz

### Frame size

45 mm

### Terminals

Screw terminals

### Coil

115 Vac, 60 Hz

### Coil voltage

115 Vac, 60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

25 A

### Series

XT IEC

### Operation

Non-reversing

### Power consumption

11 kW

## Resources

### Multimedia

[Contactors Explained](#)

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

### Specifications and datasheets

[Global Data Sheet - DILM25-10\(115V60HZ\)](#)

[Eaton Specification Sheet - DILM25-10\(115V60HZ\)](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)