

Eaton DILM25-10(RDC130)

Catalog Number: DILM25-10(RDC130)

Eaton XT IEC large contactor, 25A, 110-130 Vdc, 1NO, 25A, Frame C, 45 mm, 2, 5/7.5, 10, 15, 20 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Reversing, XT IEC series, Full voltage reversing miniature contactor, 400V, 11 kW

General specifications



Photo is representative

Product Name

Eaton XT IEC large contactor

EAN

4015082771485

Product Height

85 mm

Product Weight

0.01 lb

Certifications

UL Listed

EN 60947

IEC 60947

CSA Certified

Catalog Number

DILM25-10(RDC130)

Product Length/Depth

138 mm

Product Width

45.03 mm

Compliances

CE Marked

RoHS Compliant

defaultTaxonomyAttributeLabel

Amperage Rating

25A

HP rating - max

2, 5/7.5, 10, 15, 20 (1/3PH @120,240/208,240,480,600 V)

Number Of Poles

Three-pole

Type

Full voltage reversing miniature contactor

Voltage rating

400 V

Frame size

45 mm

Coil voltage

110-130 Vdc

Contact configuration

1 NO

Continuous ampere rating

25 A

Series

XT IEC

Operation

Reversing

Power consumption

11 kW

Resources

Multimedia

[Contactors Explained](#)

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Product Data Sheet - DILM25-10\(RDC130\)](#)

[Eaton Specification Sheet - DILM25-10\(RDC130\)](#)