

Eaton DILM25-21(RDC24)

Catalog Number: DILM25-21(RDC24)

Eaton XT IEC large contactor, 25A, 24 Vdc, 2NO-1NC, 25A, Frame C, 45 mm, 2, 5/7.5, 10, 15, 20 (1/3PH @ 120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, XT IEC series, Screw terminals, Full voltage non-reversing contactor, 11 kW

General specifications



Photo is representative

Product Name

Eaton XT IEC large contactor

EAN

4015082772109

Product Height

3.3 in

Product Weight

1.28 lb

Compliances

RoHS Compliant

CE Marked

Catalog Number

DILM25-21(RDC24)

Product Length/Depth

1.8 in

Product Width

5.8 in

Warranty

1 year

Certifications

EN 60947

UL Listed

CSA Certified

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm(80-150A); no lugs (185-2000A).

defaultTaxonomyAttributeLabel

Amperage Rating

25A

HP rating - max

2, 5/7.5, 10, 15, 20 (1/3PH @120,240/208,240,480,600 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24 Vdc

Contact configuration

2 NO, 1 NC

Continuous ampere rating

25 A

Series

XT IEC

Operation

Non-reversing

Power consumption

11 kW

Resources

Multimedia

[Contactors Explained](#)

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Global Data Sheet - DILM25-21\(RDC24\)](#)

[Eaton Specification Sheet - DILM25-21\(RDC24\)](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)