

Eaton DILM25-32(RDC24)

Catalog Number: DILM25-32(RDC24)

Eaton XT IEC large contactor, 25A, 24 Vdc, 3NO-2NC, 25A, Frame C, 45 mm, 2, 5/7.5, 10, 15, 20 (1/3PH @ 120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, XT IEC series, Screw terminals, Full voltage non-reversing contactor, 11 kW

General specifications



Photo is representative

Product Name

Eaton XT IEC large contactor

Catalog Number

DILM25-32(RDC24)

EAN

4015082772420

Product Length/Depth

1.8 in

Product Height

3.3 in

Product Width

5.8 in

Product Weight

1.36 lb

Warranty

1 year

Compliances

CE Marked

RoHS Compliant

Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm(80-150A); no lugs (185-2000A).

defaultTaxonomyAttributeLabel

Amperage Rating

25A

HP rating - max

2, 5/7.5, 10, 15, 20 (1/3PH @120,240/208,240,480,600 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24 Vdc

Contact configuration

3 NO, 2 NC

Continuous ampere rating

25 A

Series

XT IEC

Operation

Non-reversing

Power consumption

11 kW

Resources

Multimedia

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Contactors Explained

Specifications and datasheets

Eaton Specification Sheet - DILM25-32(RDC24)

Global Data Sheet - DILM25-32(RDC24)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)