

# Eaton DILM50(24V60HZ)

Catalog Number: DILM50(24V60HZ)

Eaton XT IEC contactor, 50A,24 Vac, 60 Hz, 0NO-0NC, 50A, Frame D, 55 mm, 60 Hz, 3, 7.5/ 10, 15, 30, 40 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, , Screw terminals, FVNR, 22 kW



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	DILM50(24V60HZ)
<b>EAN</b>	<b>Product Length/Depth</b>
4015082778217	2.2 in
<b>Product Height</b>	<b>Product Width</b>
4.5 in	5.2 in
<b>Product Weight</b>	<b>Warranty</b>
1.98 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
RoHS Compliant	EN 60947
	CSA Certified
	IEC 60947

## Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

50A

### HP rating - max

3, 7.5/ 10, 15, 30, 40 (1/3PH @120,240/208,240,480,600 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

24 Vac 60 Hz

### Coil voltage

24 Vac, 60 Hz

### Contact configuration

0 NO, 0 NC

### Continuous ampere rating

50 A

### Series

XT IEC

### Operation

Non-reversing

### Power consumption

22 kW

## Resources

### Specifications and datasheets

[Global Data Sheet - DILM50\(24V60HZ\)](#)

[Eaton Specification Sheet - DILM50\(24V60HZ\)](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)