

Eaton DILM50(RDC130)

Catalog Number: DILM50(RDC130)

Eaton XT IEC contactor, 50A, 110-130 Vdc, 50A, Frame D, 55 mm, 3, 7.5/ 10, 15, 30, 40 (1/3PH @ 120, 240/208, 240, 480, 600 V), Three-pole, Reversing, XT IEC series, Full voltage reversing medium contactor, 22 kW



Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	DILM50(RDC130)
EAN	Product Length/Depth
4015082778460	147 mm
Product Height	Product Width
115 mm	77 mm
Product Weight	Compliances
0.01 lb	CE Marked RoHS Compliant
Certifications	
IEC 60947 UL Listed EN 60947 CSA Certified	

defaultTaxonomyAttributeLabel

Amperage Rating

50A

HP rating - max

3, 7.5/ 10, 15, 30, 40 (1/3PH @120,240/208,240,480,600 V)

Number Of Poles

Three-pole

Type

Full voltage reversing medium contactor

Frame size

55 mm

Coil voltage

110-130 Vdc

Continuous ampere rating

50 A

Series

XT IEC

Operation

Reversing

Power consumption

22 kW

Resources

Specifications and datasheets

[Eaton Specification Sheet - DILM50\(RDC130\)](#)

[Product Data Sheet - DILM50\(RDC130\)](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)