

Eaton DILMF65(RAC120)

Catalog Number: DILMF65(RAC120)

Eaton XT IEC contactor, 65A, 120 Vdc, 0NO-0NC, 65A, Frame F, 55 mm, 5, 15/ 20, 25, 50, 60 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, XT IEC series, Screw terminals, Full voltage non-reversing contactor, 30 kW



Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	DILMF65(RAC120)
EAN	Product Length/Depth
4015081042852	2.2 in
Product Height	Product Width
4.5 in	5.2 in
Product Weight	Warranty
1.98 lb	1 year
Compliances	Certifications
CE Marked	IEC 60947
RoHS Compliant	UL Listed
	CSA Certified
	EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm(80-150A); no lugs (185-2000A).

defaultTaxonomyAttributeLabel

Amperage Rating

65A

HP rating - max

5, 15/ 20, 25, 50, 60 (1/3PH @120,240/208,240,480,600 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frame size

55 mm

Terminals

Screw terminals

Coil

120 Vdc

Coil voltage

120 Vdc

Contact configuration

0 NO, 0 NC

Continuous ampere rating

65 A

Series

XT IEC

Operation

Non-reversing

Power consumption

30 kW

Resources

Specifications and datasheets

[Global Data Sheet - DILMF65\(RAC120\)](#)

[Eaton Specification Sheet - DILMF65\(RAC120\)](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)