

# Eaton DSD922 SA

Catalog Number: DSD922 SA

Eaton Crouse-Hinds series DSD front operated pushbutton cover and device sub-assembly, 10A, Green/red, Copper-free aluminum, 2 circuits start-stop, 2 buttons, Factory sealed, 600 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series DSD front operated pushbutton cover and device sub-assembly	DSD922 SA
	UPC
	782274576282
Product Length/Depth	Product Height
3.5 in	4.34 in
Product Width	Product Weight
2.75 in	2.25 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

## Product specifications

### Voltage rating

600 Vac

### Number of cover buttons

2

### Normal position

2 circuits start-stop

### Amperage Rating

10A

### Color

Green/red

### Material

Copper-free aluminum

### Special features

Factory sealed

## Resources

### Catalogs

[DSD and DSDX Cover and Device Sub-assemblies catalog page](#)

### Certification reports

[DSD Explosionproof Cover and Device Sub-assemblies UL certification](#)

[DSD Explosionproof Cover and Device Sub-assemblies Canadian certification](#)

### Installation instructions

[IF 1424 - DSD, GFS, CPS and ENR Series Replacement Covers](#)

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

[IF 1929 - Toggle Operator for EDS, EDSX, EFD, DSD and DSDX Series](#)

### Specifications and datasheets

[Eaton Specification Sheet - DSD922 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)