

Eaton DSD925 SA HN OF AU

Catalog Number: DSD925 SA HN OF AU

Eaton Crouse-Hinds series DSD selector switch cover and device sub-assembly, 10A, HAND/OFF/AUTOMATIC, Copper-free aluminum, 3 position, 2 circuit, Factory sealed, Maintained contact, 600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series DSD selector switch cover and device sub-assembly	DSD925 SA HN OF AU
	UPC
	782274433189
Product Length/Depth	Product Height
5.1 in	4.2 in
Product Width	Product Weight
6.4 in	1 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

Product specifications

Voltage rating

600 Vac

Normal position

3 position, 2 circuit

Indicating plate markings

HAND/OFF/AUTOMATIC

Amperage Rating

10A

Material

Copper-free aluminum

Special features

Factory sealed

Type

Maintained contact

Resources

Catalogs

[DSD and DSDX Cover and Device Sub-assemblies catalog page](#)

Certification reports

[DSD Explosionproof Cover and Device Sub-assemblies Canadian certification](#)

[DSD Explosionproof Cover and Device Sub-assemblies UL certification](#)

Installation instructions

[IF 1424 - DSD, GFS, CPS and ENR Series Replacement Covers](#)

[IF 1929 - Toggle Operator for EDS, EDSX, EFD, DSD and DSDX Series](#)

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

Specifications and datasheets

[Eaton Specification Sheet - DSD925 SA HN OF AU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)