

# Eaton DSD SR30223

Catalog Number: DSD SR30223

Eaton Crouse-Hinds series DSD-SR selector switch, 30A, 1.5 HP/3 HP/5 HP/7.5 HP/10 HP, Copper-free aluminum, 1, Two-pole, 2, Double-throw without OFF with electrically isolated contacts, 600 Vac, EDS/EFS back boxes



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series DSD-SR selector switch	DSD SR30223
	UPC
	662276850156
Product Length/Depth	Product Height
2.38 in	5.875 in
Product Width	Product Weight
3.5 in	1.58 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

### NEMA Rating

3

5

12

## Product specifications

### Amperage Rating

30A

### Voltage rating

600 Vac

### Switch function

Double-throw without OFF with electrically isolated contacts

### Number Of Poles

Two-pole

### Number Of Positions

2

### Horsepower

1.50 hp, 3 hp, 5 hp, 7.50 hp, 10 hp

### Material

Copper-free aluminum

### Number of devices

1

### Used with

EDS/EFS back boxes

## Resources

### Catalogs

[DSD-SR Series Explosionproof HP Rated Selector Switch Sub-assembly catalog page](#)

### Certification reports

[DSD-SR Explosionproof HP Rated Selector Switch Sub-assembly UL certification](#)

[DSD-SR Explosionproof HP Rated Selector Switch Sub-assembly Canadian certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - DSD SR30223](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)