

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

12

3

5

Product specifications

Amperage Rating

30A

Voltage rating

600 Vac

Switch function

Double-throw with OFF with electrically isolated contacts

Number Of Poles

Two-pole

Number Of Positions

3

Used with

EDS/EFS back boxes

Resources

Catalogs

[DSD-SR Series Explosionproof HP Rated Selector Switch Sub-assembly catalog page](#)

Certification reports

[DSD-SR Explosionproof HP Rated Selector Switch Sub-assembly Canadian certification](#)

[DSD-SR Explosionproof HP Rated Selector Switch Sub-assembly UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - DSD SR30234](#)