

Eaton E49S71DP7

Catalog Number: E49S71DP7

E49 IEC Limit Switch, 1 Normally Open Contact/1 Normally Closed Contact, Rod Lever

General specifications



Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S71DP7
UPC	Product Length/Depth
782113742175	6 in
Product Height	Product Width
1.92 in	1.22 in
Product Weight	Warranty
0.5 lb	1 year
Certifications	
CSA Certified	
UL Listed	

Contact Rating

10A at 240 Vac, 1.5A at 30 Vdc

Enclosure material

Plastic

Actuator

Rod lever

Connection

Screw terminal

Contact configuration

Snap action, 1NO-1NC

Series

E49

Operating temperature - max

176 °F

Operating temperature - min

-22 °F

Environmental rating

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

Maximum AC current

10 A continuous

Maximum DC current

1.5 A at 24Vdc

Mounting method

Miniature DIN rail

Operating voltage

500 V

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E49S71DP7](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)