

Eaton E49S71EP7-20

Catalog Number: E49S71EP7-20

E49 Miniature DIN Limit Switch, Plastic Body, Offset Roller Lever, Self-extinguishing PA-6 (Glass-reinforced, Polyamide) enclosure, 10A max AC, 1.5A max DC, 1NO-1NC, 10A at 600Vac, 1.5A at 24Vdc, Screw Terminals

General specifications

Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S71EP7-20
UPC	Product Length/Depth
782113550916	1.22 in
Product Height	Product Width
3.54 in	1.2 in
Product Weight	Warranty
0.1313 lb	1 year

Contact Rating

10A at 600Vac, 1.5A at 24Vdc

Enclosure material

Self-extinguishing PA-6 (glass-reinforced, polyamide)

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Switch type

Offset roller lever

Operating temperature - max

176 °F

Operating temperature - min

-22 °F

Environmental rating

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

Maximum AC current

10 A

Maximum DC current

1.5 A

Specifications and datasheets

[Eaton Specification Sheet - E49S71EP7-20](#)