

# Eaton E49S71UP7-20

Catalog Number: E49S71UP7-20

E49 Miniature DIN Limit Switch, Plastic Body, Adj. Side Rotary, Self-extinguishing PA-6 (Glass-reinforced, Polyamide) enclosure, 10A max AC, 1.5A max DC, 1NO-1NC, 10A at 600Vac, 1.5A at 24Vdc, Screw Terminals

## General specifications



Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S71UP7-20
UPC	Product Length/Depth
782113551401	1.22 in
Product Height	Product Width
5.61 in	2.19 in
Product Weight	Warranty
0.2313 lb	1 year

Contact Rating

10A at 600Vac, 1.5A at 24Vdc

Enclosure material

Self-extinguishing PA-6 (glass-reinforced, polyamide)

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Switch type

Adjustable side rotary

Operating temperature - max

176 °F

Operating temperature - min

-22 °F

Environmental rating

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

Maximum AC current

10 A

Maximum DC current

1.5 A

Specifications and datasheets

[Eaton Specification Sheet - E49S71UP7-20](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)