

Eaton E49S73

Catalog Number: E49S73

Eaton E49 Miniature DIN Limit Switch, Plastic Body, Self-extinguishing PA-6 (Glass-reinforced, Polyamide) enclosure, 10A max AC, 1.5A max DC, 1NO-1NC, 10A at 600Vac, 1.5A at 24Vdc, Screw Terminals

General specifications



Photo is representative

Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S73
UPC	Product Length/Depth
782114982945	1.22 in
Product Height	Product Width
2.91 in	1.2 in
Product Weight	Warranty
0.1188 lb	1 year
Certifications	
UL Listed	

Type

Mechanical Limit Switches

Contact Rating

10A at 600Vac, 1.5A at 24Vdc

Enclosure material

Self-extinguishing PA-6 (glass-reinforced, polyamide)

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Operating temperature - max

176 °F

Operating temperature - min

-22 °F

Environmental rating

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

Maximum AC current

10 A

Maximum DC current

1.5 A

Specifications and datasheets

[Eaton Specification Sheet - E49S73](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)