

# Eaton E49S73CP7

Catalog Number: E49S73CP7

E49 IEC Limit Switch,2 Normally Closed Contacts,Top Push Roller Lever

## General specifications

Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S73CP7
UPC	Product Length/Depth
782114982891	1.22 in
Product Height	Product Width
3.62 in	1.2 in
Product Weight	Warranty
0.15 lb	1 year



**Contact Rating**

10A at 600Vac, 1.5A at 24Vdc

**Enclosure material**

Self-extinguishing PA-6 (glass-reinforced, polyamide)

**Connection**

Screw terminal

**Contact configuration**

1 NO-1 NC

**Switch type**

Top push roller

**Operating temperature - max**

176 °F

**Operating temperature - min**

-22 °F

**Environmental rating**

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

**Maximum AC current**

10 A

**Maximum DC current**

1.5 A

**Specifications and datasheets**

[Eaton Specification Sheet - E49S73CP7](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)