

Eaton E49S74EP7-A5

Catalog Number: E49S74EP7-A5

E49 IEC Limit Switch,2 Normally Open Contacts,Offset Roller Lever, M12 connector

General specifications

Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S74EP7-A5
UPC	Product Length/Depth
786685269252	1.22 in
Product Height	Product Width
3.54 in	1.2 in
Product Weight	Warranty
0.1313 lb	1 year



Contact Rating

10A at 600Vac, 1.5A at 24Vdc

Enclosure material

Self-extinguishing PA-6 (glass-reinforced, polyamide)

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Switch type

Offset roller lever

Operating temperature - max

176 °F

Operating temperature - min

-22 °F

Environmental rating

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

Maximum AC current

10 A

Maximum DC current

1.5 A

Specifications and datasheets

[Eaton Specification Sheet - E49S74EP7-A5](#)