

Eaton E49S74UP7

Catalog Number: E49S74UP7

E49 IEC Limit Switch, 2 Normally Open Contacts, Adjustable Roller Lever

General specifications



Photo is representative

Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49S74UP7
UPC	Product Length/Depth
782114982860	1.22 in
Product Height	Product Width
5.61 in	2.19 in
Product Weight	Warranty
0.2313 lb	1 year
Certifications	
UL Listed	

Contact Rating

10A at 600Vac, 1.5A at 24Vdc

Enclosure material

Self-extinguishing PA-6 (glass-reinforced, polyamide)

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Switch type

Adjustable side rotary

Operating temperature - max

176 °F

Operating temperature - min

-22 °F

Environmental rating

NEMA 4, NEMA 4X, NEMA 6P, NEMA 13, IP65

Maximum AC current

10 A

Maximum DC current

1.5 A

Specifications and datasheets

[Eaton Specification Sheet - E49S74UP7](#)