

Eaton E50KL201SPL

Catalog Number: E50KL201SPL

Limit Switch Operator, E50, Accessory, Adjustable roller, Used with side rotary, Nylatron high grade stainless steel

General specifications



Photo is representative

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL201SPL

UPC
782113761176

Product Length/Depth
4.6 in

Product Height
0.84 in

Product Width
0.75 in

Product Weight
0.1 lb

Warranty
1 year

Compliances
RoHS Compliant

Certifications
UL Listed
CSA Certified
CE

Type

Accessory

Used with

Used with side rotary

Actuator

Adjustable roller

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Material

Nylatron high grade stainless steel

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL201SPL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)