

Eaton E50KL203

Catalog Number: E50KL203

E50 Series Limit Switch Operator, Lever for Side Rotary Switches,
Roller: Nylatron enclosure, Lever: Die Cast Zinc

General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL203
	UPC
	782113298511
Product Length/Depth	Product Height
1.9 in	2.87 in
Product Width	Product Weight
0.93 in	0.06 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified CE	Lever length is from the operating shaft axis to the roller axis

Enclosure material

Lever: die Cast Zinc

Roller: nylatron

Switch type

Lever for side rotary switches

Operating temperature - max

201 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Catalogs

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - E50KL203



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia