

Eaton E50KL226

Catalog Number: E50KL226

Limit Switch Operator, E50 Heavy Duty Plug In, Accessory, Adjustable rod, Used with side rotary, Bendable steel

General specifications

Product Name Catalog Number

Eaton E50 NEMA heavy duty plug-in limit E50KL226
switch operator

UPC
782113290966

Product Length/Depth

12 in

Product Height

0.38 in

Product Width

1.12 in

Product Weight

0.3 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed
CSA Certified
CE



Type

Accessory

Used with

Used with side rotary

Actuator

Adjustable rod

Series

E50 heavy duty plug in

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Material

Bendable steel

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL226](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)