

# Eaton E50KL35

Catalog Number: E50KL35

Limit Switch Lever, E50, Accessory, Clamp, Used with adjustable 0.19 (4.8) diameter rods, Stainless steel

## General specifications



Product Name	Catalog Number
--------------	----------------

Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL35
---	---------

UPC

782113453910

Product Length/Depth	Product Height
----------------------	----------------

0.64 in

0.38 in

Product Width	Product Weight
---------------	----------------

1.12 in

0.15 lb

Warranty	Compliances
----------	-------------

1 year

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE

**Type**

Accessory

**Used with**

Used with adjustable 0.19 (4.8) diameter rods

**Actuator**

Clamp

**Series**

E50

**Operating temperature - max**

200 °F

**Operating temperature - min**

10 °F

**Environmental rating**NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67**Material**

Stainless steel

**Catalogs**[Eaton's Volume 8—Sensing Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E50KL35](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)