

# Eaton E50KL377

Catalog Number: E50KL377

Limit Switch Operator, E50, Accessory, Standard roller, 0.96 in-oz min. return, Used with side rotary, Nylatron

## General specifications



|                                                         |                |
|---------------------------------------------------------|----------------|
| Product Name                                            | Catalog Number |
| Eaton E50 NEMA heavy duty plug-in limit switch operator | E50KL377       |

|              |
|--------------|
| UPC          |
| 782113297873 |

|                      |
|----------------------|
| Product Length/Depth |
| 2.22 in              |

|                |
|----------------|
| Product Height |
| 1.33 in        |

|               |
|---------------|
| Product Width |
| 0.75 in       |

|                |
|----------------|
| Product Weight |
| 0.15 lb        |

|          |
|----------|
| Warranty |
| 1 year   |

|                |
|----------------|
| Compliances    |
| RoHS Compliant |

|                |
|----------------|
| Certifications |
| UL Listed      |
| CSA Certified  |
| CE             |

Type

Accessory

Used with

Used with side rotary

Actuator

Standard roller

Torque rating

0.96 in-oz min return

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

Material

Nylatron

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL377](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)