

# Eaton E51DP4

Catalog Number: E51DP4

Eaton Photoelectric Sensor Head, E51, Diffuse Reflective, 41 in range, Right Angle



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton E51 NEMA limit switch photoelectric sensor	E51DP4
	<b>UPC</b>
	782113142937
<b>Product Length/Depth</b>	<b>Product Height</b>
1.84 in	2.03 in
<b>Product Width</b>	<b>Product Weight</b>
1.54 in	0.18 lb
<b>Warranty</b>	<b>Compliances</b>
3 year	CE Marked
<b>Certifications</b>	
CSA Certified	
UL Listed	

**Type**

Photoelectric Sensor

**Enclosure material**

Plastic

**Series**

E51

**Sensor type**

Polarized retroreflective

**Operating temperature - max**

158 °F

**Operating temperature - min**

-13 °F

**Environmental rating**NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,  
NEMA 12, NEMA 13, IP67**Catalogs**[Eaton's Volume 8—Sensing Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E51DP4](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)