

Eaton E51DT1

Catalog Number: E51DT1

Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor Head, E51, 0.51 in range, Top Sensing, Shielded, Standard frequency



General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton E51 NEMA limit switch inductive proximity sensor | E51DT1 |
| | UPC |
| | 782113344904 |
| Product Length/Depth | Product Height |
| 1.38 in | 1.51 in |
| Product Width | Product Weight |
| 1.51 in | 0.1 lb |
| Warranty | Certifications |
| 1 year | UL Listed |
| | CSA Certified |

defaultTaxonomyAttributeLabel

Actuator function

Shielded

Frequency rating

Standard

Enclosure material

Plastic

Series

E51

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51DT1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)