

Eaton E51DT2

Catalog Number: E51DT2

Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor Head, E51, 0.51 in range, Top Sensing, Shielded, Alternate frequency



General specifications

Product Name	Catalog Number
Eaton E51 NEMA limit switch inductive proximity sensor	E51DT2
	UPC
	782113344911
Product Length/Depth	Product Height
1.38 in	1.51 in
Product Width	Product Weight
1.51 in	0.22 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Actuator function

Shielded

Frequency rating

Alternate

Enclosure material

Plastic

Series

E51

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51DT2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia