

Eaton E51DT6

Catalog Number: E51DT6

Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor Head, E51, 0.94 in range, Top Sensing, Unshielded, Alternate frequency

General specifications



Product Name	Catalog Number
Eaton E51 NEMA limit switch inductive proximity sensor	E51DT6
	UPC
	782113358970
Product Length/Depth	Product Height
1.38 in	1.51 in
Product Width	Product Weight
1.51 in	0.1 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed

Actuator function

Unshielded

Frequency rating

Alternate

Enclosure material

Plastic

Series

E51

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51DT6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)