

Eaton E51KF7315

Catalog Number: E51KF7315

Eaton Photoelectric Sensor Fiber Optic Cable, E51, Fiber Optic, Straight, 3 ft, Unthreaded

General specifications



Product Name	Catalog Number
Eaton E51 NEMA limit switch photoelectric sensor fiber optic cable	E51KF7315
	UPC
	782113446493
Product Length/Depth	Product Height
1.5 in	72 in
Product Width	Product Weight
0.31 in	0.3626 lb
Warranty	Certifications
3 year	UL Listed CSA Certified

Type

Fiber Optic

Cable type

Unthreaded

Enclosure material

Stainless steel

Series

E51

Cord length

36 ft

Operating temperature - max

480 °F

Operating temperature - min

-50 °F

Environmental ratingNEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP67**Catalogs**[Eaton's Volume 8—Sensing Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E51KF7315](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)