

Eaton E51RC

Catalog Number: E51RC

Eaton E51 NEMA limit switch inductive proximity sensor, Assembled Inductive Proximity Fiber Optic Sensor, E51, Screw Terminals, 4-wire, 120 Vac

General specifications



Product Name	Catalog Number
Eaton E51 NEMA limit switch inductive proximity sensor	E51RC
	UPC
	782113107202
Product Length/Depth	Product Height
2.92 in	1.06 in
Product Width	Product Weight
1.54 in	0.45 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

Type

Assembled Inductive Proximity Fiber Optic Sensor

Enclosure material

Die cast zinc

Connection

Screw terminal

Series

E51

Number of wires

4

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Operating voltage

120 Vac

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51RC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia