

# Eaton E51RCP5

Catalog Number: E51RCP5

Eaton E51 NEMA limit switch inductive proximity sensor, E51 Series Receptacle, Die Cast Zinc enclosure, 5 Pin Mini Connector.



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton E51 NEMA limit switch inductive proximity sensor	E51RCP5
	<b>UPC</b>
	782113146942
<b>Product Length/Depth</b>	<b>Product Height</b>
5.38 in	1.62 in
<b>Product Width</b>	<b>Product Weight</b>
1.81 in	0.6313 lb
<b>Warranty</b>	<b>Compliances</b>
1 year	CE Marked
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	Epoxy filled receptacle with prewired Mini-Connector

Enclosure material

Die cast zinc

Connection

5-pin mini connector

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,  
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51RCP5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)