

Eaton E57-30GS10-AAB

Catalog Number: E57-30GS10-AAB

E57 Two-Wire Series Tubular Inductive Proximity Sensor, 1.18 dia, Straight, Sensor dist: 10 mm, 200 mA max AC, 2 - Wire AC, NO, 200 mA at 250 Vac, 3 Pin Dual Key Micro Connector, 20-250 Vac input, < 1% accuracy, None, Shielded



Photo is representative

General specifications

Product Name	Catalog Number
Eaton E57 inductive proximity sensor	E57-30GS10-AAB
UPC	Product Length/Depth
782114665220	1.18 in
Product Height	Product Width
3.19 in	1.18 in
Product Weight	Warranty
0.375 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

defaultTaxonomyAttributeLabel

Type

Inductive Proximity Sensor; Tubular; Global

Contact Rating

200 mA at 250 Vac

Actuator function

Shielded

Accuracy

< 1%

Indicator type

LED

Enclosure material

Nickel plated brass

Connection

3-pin dual key micro connector

Contact configuration

2-wire AC, NO

Series

E57

Sensor type

Inductive proximity

Environmental rating

IP67, IP69K

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Maximum AC current

200 mA

Input voltage

20-250 Vac

LED indicator

Output status: red

Protection

None

Resources

Brochures

[Global Series inductive proximity sensors](#)

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

Multimedia

[We make what matters](#)

Specifications and datasheets

[Eaton Specification Sheet - E57-30GS10-AAB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)