

Eaton E57-30GS10-DDB

Catalog Number: E57-30GS10-DDB

Inductive Global Proximity Sensor, E57, Straight, 30 mm, Shielded, Output ON, M12, 100 mA at 10-30 Vdc, 4 pin, <2.0% sensing range, 2-wire DC, NO, 10-30 Vdc



General specifications

Product Name	Catalog Number
Eaton E57 inductive proximity sensor	E57-30GS10-DDB
UPC	Product Length/Depth
782114665121	2.95 in
Product Height	Product Width
1.18 in	1.18 in
Product Weight	Warranty
0.2 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

defaultTaxonomyAttributeLabel

Type

E57

Contact Rating

100 mA at 10-30 Vdc

Actuator function

Shielded

Accuracy

< 2.0% sensing range

Enclosure material

Nickel plated brass

Connection

M12

Contact configuration

2-wire DC, NO

Series

E57

Environmental rating

IP67, IP69K

Temperature rating

-13 to 158 °F

Number of pins

4

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Maximum DC current

100 mA

Input voltage

10-30 Vdc

Size

30 mm

LED indicator

Output ON

Protection

Resources

Brochures

[Global Series inductive proximity sensors](#)

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

Multimedia

[We make what matters](#)

Specifications and datasheets

[Eaton Specification Sheet - E57-30GS10-DDB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)