

# Eaton E57FAL30A2SA-M

Catalog Number: E57FAL30A2SA-M

E57 Series Tubular Metal Faced Inductive Proximity Sensor, 1.18 dia, Straight, Sensor dist: 10 mmdist, 100 mA max AC, 2 - Wire AC, NO, 100 mA at 250 Vac, 3 Pin Dual Key Micro Connector, 20-250 Vac input, < 3% accuracy, None, Shielded

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton E57 inductive proximity sensor	E57FAL30A2SA-M
<b>UPC</b>	<b>Product Length/Depth</b>
782113974965	1.18 in
<b>Product Height</b>	<b>Product Width</b>
3.7 in	1.18 in
<b>Product Weight</b>	<b>Warranty</b>
0.37 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	CSA Certified
	UL Listed

## defaultTaxonomyAttributeLabel

### Contact Rating

100 mA at 250 Vac

### Actuator function

Shielded

### Accuracy

< 3%

### Enclosure material

Stainless steel

### Connection

3-pin dual key micro connector

### Contact configuration

2-wire AC, NO

### Series

E57

### Sensor type

Inductive proximity

### Environmental rating

NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13,  
IP67

### Operating temperature - max

158 °F

### Operating temperature - min

-13 °F

### Maximum AC current

100 mA

### Input voltage

20-250 Vac

### LED indicator

Output status: red

### Protection

None

## Resources

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

[Product Range Catalog Sensors – products, basic information, applications](#)

### Multimedia

[We make what matters](#)

### Specifications and datasheets

[Eaton Specification Sheet - E57FAL30A2SA-M](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)