

Eaton EBBRA304 WT30 3

Catalog Number: EBBRA304 WT30 3

Eaton Crouse-Hinds series Arktite EBBR interlocked receptacle, 30A, 30A circuit breaker, Three-wire, four-pole, Solid door, With breaker, Style 2, Cutler-Hammer, Copper-free aluminum, Spring door, 1-1/2", 480 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite EBBR interlocked receptacle	EBBRA304 WT30 3
	UPC
	782274417936
Product Length/Depth	Product Height
14.06 in	22.85 in
Product Width	Product Weight
10.25 in	95 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

3R

7

9

12

Product specifications

Receptacle style

Spring door

Enclosure type

With breaker

Amperage Rating

30A

Grounding style

Style 2

Configuration

Three-wire, four-pole

Trade size

1-1/2"

Voltage rating

480 Vac/250 Vdc

Circuit breaker amperage

30A

Manufacturer

Cutler-Hammer

Door style

Solid

Material

Copper-free aluminum

Resources

3D models

[SP3D Design Package - Arktite EBBR Explosionproof Interlocked Receptacles with Enclosed Circuit Breakers](#)

Catalogs

[Arktite EBBR Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[Arktite EBBR Explosionproof Interlock Receptacles with Enclosed Circuit Breakers Canadian certification](#)

[Arktite EBBR Explosionproof Interlock Receptacles with Enclosed Circuit Breakers UL certification](#)

Installation instructions

IF 1311 - EBBR Replacement Kit

IF 1224 - EBBR Interlocked Receptacle

Specifications and datasheets

Eaton Specification Sheet - EBBRA304 WT30 3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)