

Eaton EBBRB104

Catalog Number: EBBRB104

Eaton Crouse-Hinds series Arktite EBBR receptacle enclosure, 100A, Three-wire, four-pole, Solid door, Without breaker, Style 2, Copper-free aluminum, 1-1/2", Size B enclosure



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite EBBR receptacle enclosure	EBBRB104
	UPC
	782274418346
Product Length/Depth	Product Height
14.06 in	32.2 in
Product Width	Product Weight
10.25 in	131 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

3R

7

9

12

Product specifications

Enclosure type

Without breaker

Amperage Rating

100A

Grounding style

Style 2

Configuration

Three-wire, four-pole

Trade size

1-1/2"

Door style

Solid

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds EBBRB104 3D drawing](#)

3D models

[SP3D Design Package - Arktime EBBR Explosionproof Interlocked Receptacles with Enclosed Circuit Breakers](#)

Catalogs

[Arktime EBBR Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[Arktime EBBR Explosionproof Interlock Receptacles with Enclosed Circuit Breakers Canadian certification](#)

[Arktime EBBR Explosionproof Interlock Receptacles with Enclosed Circuit Breakers UL certification](#)

Installation instructions

[IF 1311 - EBBR Replacement Kit](#)

[IF 1224 - EBBR Interlocked Receptacle](#)

Specifications and datasheets

[Eaton Specification Sheet - EBBRB104](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)