

Eaton EBY2682

Catalog Number: EBY2682

Eaton Crouse-Hinds series EBY portable cord connector, Non-armoured and tray cable, Aluminum, Outer sheath min/max: 0.375-0.500", Explosionproof, 3/4" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series EBY portable cord connector	EBY2682
	UPC
	782274249605
Product Length/Depth	Product Height
6.25 in	2.06 in
Product Width	Product Weight
2.06 in	1.25 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Product specifications

Protection type

Explosion-proof

Cable type

Tray cable

Non-armoured

Gland type

Portable cord connector

Thread Size

3/4"

Thread type

NPT

Outer sheath (min/max)

0.375-0.500"

Material

Aluminum

Resources

Catalogs

[Crouse-Hinds series EBY catalog page](#)

Certification reports

[CGBS and EBY Explosionproof Portable Cord Connectors UL certification \(EBY\)](#)

[CGBS and EBY Explosionproof Portable Cord Connectors Canadian certification \(EBY\)](#)

Installation instructions

[IF 389 - EBY Portable Cord Connector](#)

Specifications and datasheets

[Eaton Specification Sheet - EBY2682](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)