

# Eaton ECL03C1A3A-S3

Catalog Number: ECL03C1A3A-S3

Eaton CN35 electrically held lighting contactor, HAND/OFF/AUTO selector switch, 30 A, 110 V/50 Hz, 120 V/60 Hz, 20 A, NEMA 1, Painted steel, 45 mm, Three-pole, Electrically held, A202 Series, Non-combination electrically held



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CN35 electrically held lighting contactor	ECL03C1A3A-S3
	<b>UPC</b>
	786685357744

<b>Product Length/Depth</b>	<b>Product Height</b>
7.73 in	13.21 in

<b>Product Width</b>	<b>Product Weight</b>
5.84 in	13.1 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	cUL Listed

### Catalog Notes

Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

## defaultTaxonomyAttributeLabel

### Accessories

HAND/OFF/AUTO selector switch

### Amperage Rating

20A

### Number Of Poles

Three-pole

### Type

Non-combination electrically held

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact rating

30 A

### Enclosure

NEMA 1

### Enclosure material

Painted steel

### Frame size

45 mm

### Operation

Electrically held

### Series

A202

## Resources

### Brochures

[Lighting contactors](#)

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECL03C1A3A-S3](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)