

# Eaton ECN2404CAC

Catalog Number: ECN2404CAC

Eaton Freedom NEMA enclosed control , NEMA 4X , Combination non-reversing starter—circuit breaker , With control power transformer , 7A , Three-phase , 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Freedom NEMA enclosed control	ECN2404CAC
UPC	Product Length/Depth
782114194003	31 in
Product Height	Product Width
11 in	12 in
Product Weight	Warranty
0.1 lb	1 year

## Certifications

UL Listed file E1491  
Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Enclosure

NEMA 4X

### Type

Combination non-reversing starter—circuit breaker

### Accessories

With control power transformer

### Circuit breaker rating

7A

### Phase

Three-phase

### Size

NEMA size 0

### System voltage

460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary  
control power transformer

## Resources

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECN2404CAC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)