

Eaton EDS2184 SA XT

Catalog Number: EDS2184 SA XT

Eaton Crouse-Hinds series EDS pushbutton control station, With pushbuttons, XT, Copper-free aluminum, Single circuit universal, 1, Single-gang, 1, Dead end, 3/4", 600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EDS pushbutton control station	EDS2184 SA XT
	UPC
	662276630451
Product Length/Depth	Product Height
8.5 in	6 in
Product Width	Product Weight
3.5 in	3.7 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class II, Division 1

Class III

Class I, Division 1

Class I, Division 2

Class II, Division 2

NEMA Rating

9

7

3

Product specifications

Enclosure type

With pushbuttons

Voltage rating

600 Vac

Number of gangs

Single-gang

Number of pushbuttons

1

Number of devices

1

Normal position

Single circuit universal

Indicating plate markings

XT

Style

Dead end

Trade size

3/4"

Material

Copper-free aluminum

Resources

3D models

[SP3D Design Package - EDS and EFS Explosionproof Control Stations](#)

Catalogs

[EDS/EDSX Hazardous Area Control Stations catalog page](#)

Certification reports

[EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations UL certification](#)

[EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations Canadian certification](#)

Installation instructions

[IF 372 - EDS Notice](#)

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

[IF 328 - EDS, EFS, EDSC and EFSC Single- and Two-gang Device Bodies](#)

Specifications and datasheets

Eaton Specification Sheet - EDS2184 SA XT



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia