

Eaton EDS315

Catalog Number: EDS315

Eaton Crouse-Hinds series EDS pushbutton control station, With pushbuttons, Start, Stop, Feraloy iron alloy, Two circuit, 2, Single-gang, 2, Dead end, 1", 600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EDS pushbutton control station	EDS315
	UPC
	782274763576
Product Length/Depth	Product Height
3.5 in	5.91 in
Product Width	Product Weight
5.81 in	8.45 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

Product specifications

Enclosure type

With pushbuttons

Voltage rating

600 Vac

Number of gangs

Single-gang

Number of pushbuttons

2

Number of devices

2

Normal position

Two circuit

Indicating plate markings

Start, Stop

Style

Dead end

Trade size

1"

Material

Feraloy iron alloy

Resources

3D models

[SP3D Design Package - EDS and EFS Explosionproof Control Stations](#)

Catalogs

[EDS/EDSX Hazardous Area Control Stations catalog page](#)

Certification reports

[EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations Canadian certification](#)

[EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations UL certification](#)

Installation instructions

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

[IF 328 - EDS, EFS, EDSC and EFSC Single- and Two-gang Device Bodies](#)

[IF 372 - EDS Notice](#)

Specifications and datasheets

Eaton Specification Sheet - EDS315



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)