

# Eaton EDSC2129

Catalog Number: EDSC2129

Eaton Crouse-Hinds series EDS snap switch control station, 20A, With switch, With two 3/4" hubs, Feraloy iron alloy, 1, Single-gang, Single-pole, 120-277V, Factory sealed, Through feed, Single-pole, 3/4", 120-277 Vac



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series EDS snap switch control station	EDSC2129
	<b>UPC</b>
	782274765624
<b>Product Length/Depth</b>	<b>Product Height</b>
5.06 in	5.875 in
<b>Product Width</b>	<b>Product Weight</b>
3.5 in	8.5 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

## Product specifications

### Enclosure type

With switch

### Trade size

3/4"

### Number Of Poles

Single-pole

### Switch function

Single-pole

### Number of gangs

Single-gang

### Style

Through feed

### Voltage rating

120-277 Vac

### Amperage Rating

20A

### Hub style

With two 3/4" hubs

### Number of devices

1

### Primary voltage range

120-277V

### Material

Feraloy iron alloy

### Special features

Factory sealed

## Resources

### Catalogs

[EDS and EDSX Fully Assembled Snap Switches catalog page](#)

### Certification reports

[EDS and EFD Explosionproof Snap Switches Canadian certification - industrial control panels and assemblies](#)

[EDS and EFD Explosionproof Snap Switches UL certification - industrial](#)

control panels and assemblies

EDS and EFD Explosionproof Snap Switches Canadian certification - snap switches

EDS and EFD Explosionproof Snap Switches UL certification - snap switches

### Installation instructions

IF 242 - EDS and EDSC Control Stations

IF 328 - EDS, EFS, EDSC and EFSC Single- and Two-gang Device Bodies

### Specifications and datasheets

Eaton Specification Sheet - EDSC2129



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)