

Eaton EFDC3419

Catalog Number: EFDC3419

Eaton Crouse-Hinds series EFD manual motor starter switch, 20A/30A, With switch, 7.5 HP/15 HP, General Electric starter, Feraloy iron alloy, Single-gang, Three-pole, Through feed, 1", 240/600 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series EFD manual motor starter switch	EFDC3419
	UPC
	782274275802
Product Length/Depth	Product Height
3.5 in	6.97 in
Product Width	Product Weight
4.88 in	8 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Enclosure

With switch

Manufacturer

General Electric

Number of gangs

Single-gang

Number Of Poles

Three-pole

Style

Through feed

Trade size

1"

Voltage rating

240 Vac/600 Vac

Horsepower

7.5 hp/15 hp

Amperage Rating

20 A/30 A

Material

Feraloy iron alloy

Resources

3D models

[SP3D Design Package - EDS and EFD Explosionproof Motor Starters](#)

Catalogs

[EFD Series Explosionproof Motor Starters catalog page](#)

Certification reports

[EDS and EFD Explosionproof Motor Starters Canadian certification](#)

[EDS and EFD Explosionproof Motor Starters UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - EFDC3419](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)