

# Eaton EJB121206 MP S598

Catalog Number: EJB121206 MP S598

Eaton Crouse-Hinds series EJB junction box, 12" x 12" x 6", With hinge, Copper-free aluminum, Mounting plate kit, hinges mounted on left side, Style C



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EJB junction box	EJB121206 MP S598
	UPC
	782274585635
Product Length/Depth	Product Height
17.06 in	17.06 in
Product Width	Product Weight
8.88 in	88.1 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

3R

4

7

9

### Ingress protection (IP) ratings

IP66

## Product specifications

### Enclosure size

12" x 12" x 6"

### Style

C

### Material

Copper-free aluminum

### Hinge

With hinge

### Special features

Mounting plate kit, hinges mounted on left side

## Resources

### 3D models

[SP3D Design Package - EJB Explosionproof Enclosures](#)

### Catalogs

[Crouse-Hinds series EJB Explosionproof Enclosures catalog page](#)

### Certification reports

[EJB Explosionproof Enclosures UL certification](#)

[EJB Explosionproof Enclosures Canadian certification](#)

### Installation instructions

[IF 931 - EJB, Style C Model M82 Series Junction Boxes](#)

[IF 1107 - Mounting Plate Kit](#)

### Specifications and datasheets

[Eaton Specification Sheet - EJB121206 MP S598](#)

[EJB Style C Enclosures](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)