

# Eaton EJB241208 S598

Catalog Number: EJB241208 S598

Eaton Crouse-Hinds series EJB junction box, 24" x 12" x 8", With hinge, Copper-free aluminum, Hinges mounted on left side, Style C



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EJB junction box	EJB241208 S598
	UPC
	782274435428
Product Length/Depth	Product Height
13.75 in	17.56 in
Product Width	Product Weight
29.56 in	190 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

3R

4

7

9

### Ingress protection (IP) ratings

IP66

## Product specifications

### Enclosure size

24" x 12" x 8"

### Style

C

### Material

Copper-free aluminum

### Hinge

With hinge

### Special features

Hinges mounted on left side

## Resources

### 3D CAD drawing package

Eaton Crouse-Hinds EJB241208 S598 3D drawing

### 3D models

SP3D Design Package - EJB Explosionproof Enclosures

### Catalogs

Crouse-Hinds series EJB Explosionproof Enclosures catalog page

### Certification reports

EJB Explosionproof Enclosures Canadian certification

EJB Explosionproof Enclosures UL certification

### Installation instructions

IF 931 - EJB, Style C Model M82 Series Junction Boxes

### Specifications and datasheets

Eaton Specification Sheet - EJB241208 S598

EJB Style C Enclosures



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)