

Eaton EMP0098 J1 LED

Catalog Number: EMP0098 J1 LED

Eaton Crouse-Hinds series EMP illuminated pushbutton operator, Red, Two normally open, two normally closed, LED pilot light, 120 Vac

General specifications



Product Name

Eaton Crouse-Hinds series EMP illuminated pushbutton operator

Catalog Number

EMP0098 J1 LED

UPC

782274239101

Product Length/Depth

6.56 in

Product Height

2.63 in

Product Width

2.63 in

Product Weight

1.11 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

Product specifications

Contact arrangement

Two normally open, two normally closed

Color

Red

Voltage rating

120 Vac

Special features

LED pilot light

Resources

Catalogs

[EMP and EMPS Hazardous Area Operators catalog page](#)

Installation instructions

[IF 872 - EMP/EMPS Barrel Assemblies Panel Mounted Enclosures](#)

[IF 1702 - EMP/EMPS Barrel Assemblies - ATEX and IEC version](#)

Specifications and datasheets

[Eaton Specification Sheet - EMP0098 J1 LED](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)