

Eaton ENC5151 CAN

Catalog Number: ENC5151 CAN

15A 125V CONN UNIT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENC connector	ENC5151 CAN
	UPC
	662276083912
Product Length/Depth	Product Height
7.63 in	3.06 in
Product Width	Product Weight
2.88 in	0.5 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

3R

Product specifications

Amperage Rating

15A

Voltage rating

125 Vac

NEMA configuration

5-15R

Cord range

0.39-1.20"

Material

Copper-free aluminum

Resources

Catalogs

[Ark-Gard ENC Explosionproof NEMA Locking Devices catalog page](#)

Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices](#)

[Canadian certification - ENC](#)

Installation instructions

[IF 1476 - ENC Series Connectors Model M4](#)

Specifications and datasheets

[Eaton Specification Sheet - ENC5151 CAN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)