

Eaton ENR31202

Catalog Number: ENR31202

Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly, 20A, Single, 50-400 Hz, Copper-free aluminum, 6-20R, Single-gang, Dead end, 1", 250 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly	ENR31202
	UPC
	782274311067
Product Length/Depth	Product Height
8 in	6.72 in
Product Width	Product Weight
3.5 in	7.15 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Number of gangs

Single-gang

Amperage Rating

20A

Voltage rating

250 Vac

Style

Dead end

Trade size

1"

NEMA configuration

6-20R

Cover type

Single

Material

Copper-free aluminum

Frequency rating

50-400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ENR31202 3D drawing](#)

Catalogs

[Ark-Gard ENR Value Explosionproof NEMA Locking Devices catalog page](#)

Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

Installation instructions

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

Specifications and datasheets

[Eaton Specification Sheet - ENR31202](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)