

Eaton ENR32151

Catalog Number: ENR32151

Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly, 15A, Double, 50-400 Hz, Copper-free aluminum, 5-15R, Two-gang, Dead end, 1", 125 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly	ENR32151
	UPC
	662276480230
Product Length/Depth	Product Height
8 in	6.72 in
Product Width	Product Weight
7.56 in	13.8 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Number of gangs

Two-gang

Amperage Rating

15A

Voltage rating

125 Vac

Style

Dead end

Trade size

1"

NEMA configuration

5-15R

Cover type

Double

Material

Copper-free aluminum

Frequency rating

50-400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ENR32151 3D drawing](#)

Catalogs

[Ark-Gard ENR Value Explosionproof NEMA Locking Devices catalog page](#)

Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

Installation instructions

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

Specifications and datasheets

[Eaton Specification Sheet - ENR32151](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)